



Main

Range	ClimaSys
Product name	ClimaSys CC
Product or Component Type	Electronic hygrotherm
Temperature setting range	-40...176 °F (-40...80 °C)
Humidity setting range	20...80 %
Display Type	OLED screen
Information Displayed	Relative humidity Temperature in °C Temperature in °F

Complementary

Input voltage	9...30 V AC/DC
Sensor Type	Optional NTC external sensor
Maximum switching capacity	4 A 30 V AC/DC
Electrical connection	8 connectors 2.5 mm ²
Mounting Mode	Clipped By screws
Height	External 3.35 in (85 mm)
Width	External 2.20 in (56 mm)
Depth	External 1.73 in (44 mm)
Mounting Location	On mounting plate 35 mm DIN rail Cross rails Spacial upright
Ambient Air Temperature for Operation	-40...176 °F (-40...80 °C)
Hysteresis	2 K programmed value
Hysteresis	3 %
Number of outputs	2 ventilation/heating function
Material	PC
Color	Light gray
Flame retardance	Self-extinguishing conforming to UL94 (material V0)
Product Certifications	UR

Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	3606480152573
Returnability	No
Country of origin	ES

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.17 in (5.5 cm)
Package 1 Width	2.95 in (7.5 cm)
Package 1 Length	3.35 in (8.5 cm)
Package 1 Weight	4.94 oz (140.0 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	75
Package 2 Height	15.75 in (40.0 cm)
Package 2 Width	15.75 in (40.0 cm)
Package 2 Length	23.62 in (60.0 cm)
Package 2 Weight	24.25 lb(US) (11.0 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------