



Main

Range	Thalassa
Accessory / separate part category	Enclosure accessory
Product or Component Type	Door
Application	Multi-purpose
For enclosure nominal dimensions	-
Mounting Location	Front side
Range compatibility	Thalassa (Thalassa PLM)
Device composition	1 door 1 handle 4 fixing brackets

Complementary

Material	Polyester charged with fibreglass
Color	Gray RAL 7035)
Lock type	Lock 5 mm double bar
Number of locks	2
Door type	Internal plain
Door opening side	Reversible 110 °)
Height	Grid pattern 12.40 in (315 mm)
Width	Grid pattern 8.07 in (205 mm)
Depth	Available depth between enclosure door 1.02 in (26 mm) Available depth between rear 5.98 in (152 mm)

Ordering and shipping details

Category	80034-ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	3606480774188
Returnability	Yes
Country of origin	ES

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.69 in (4.3 cm)
Package 1 Width	10.83 in (27.5 cm)
Package 1 Length	15.55 in (39.5 cm)
Package 1 Weight	33.86 oz (960.0 g)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile