



## Main

Range of Product	Lighting and power sockets
Accessory / separate part category	Lighting accessory
Product or Component Type	Lamp
Device Application	Multi-purpose
Device composition	Fixing elements Lamp switch

## Complementary

Outlet standard deviation	Without socket
Rated lamp wattage	11 W
[Ue] rated operational voltage	220 V 50/60 Hz
Bulb base	2G7
Bulb type	Fluorescent
Control Type	Built-it switch
Luminous flux	900 lm
Service life in hours	8000 h
Electrical connection	Screw connector <= 2.5 mm <sup>2</sup>
Mounting Location	Top front of enclosure
Mounting Support	DIN rail Upright Metal parts Cross rails
Fixing Mode	Magnetic fixing Screws Clip-in
Range compatibility	Spacial (Spacial S3D) Spacial (Spacial CRN) Thalassa (Thalassa PLA) Thalassa (Thalassa PLM) Spacial (Spacial SFX) Spacial (Spacial SMX) Spacial (Spacial SF) Spacial (Spacial SM)
Material	Light gray plastic
Height	1.57 in (40 mm)
Width	14.65 in (372 mm)
Depth	2.48 in (63 mm)

## Environment

IP degree of protection	IP20 conforming to IEC 60529
Electrical Insulation Class	Class II
Flame retardance	V0 conforming to UL 94
Electromagnetic compatibility	Emission standard for industrial environments IEC 61000-6-4
Standards	UL 508 A
Product Certifications	VDE

Ambient air temperature for operation	3...149 °F (-16...65 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)

### Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	03606480421075
Returnability	No
Country of origin	CN

### Contractual warranty

Warranty	18 months
----------	-----------