



Main

Range of Product	I-Line
Product or Component Type	Enclosure
Device Application	Panelboard

Complementary

Line Rated Current	800 A
Cover type	Lockable cover
Mounting Mode	Wall mount
Product Weight	75 lb(US) (34.02 kg)
Height	48 in (1219.20 mm)
Depth	9.5 in (241.30 mm)

Environment

NEMA Degree of Protection	NEMA 1
Standards	UL CSA

Ordering and shipping details

Category	07979-I-LINE RTA N1 PB BOX - STD
Discount Schedule	PE1A
GTIN	785901235910
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.50 in (24.13 cm)
Package 1 Width	32.50 in (82.55 cm)
Package 1 Length	48.00 in (121.92 cm)
Package 1 Weight	75.00 lb(US) (34.019 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile