



### Main

Product range	Thorsman TET
Product type	Grommet
Colour	Grey
Quantity per package	Set of 50

### Complementary

Material	EPDM
ISO thread	M25
Cable outer diameter	0.39...0.55 in (10...14 mm)
Drilling diameter	1.00 in (25.3 mm)

### Environment

IP-Class	IP67
----------	------

### Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	3606480163814
Returnability	No
Country of origin	FR

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.18 in (3 cm)
Package 1 Width	1.18 in (3 cm)
Package 1 Length	1.26 in (3.2 cm)
Package 1 Weight	0.28 oz (8 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	7.87 in (20 cm)
Package 2 Width	5.51 in (14 cm)
Package 2 Length	1.97 in (5 cm)
Package 2 Weight	14.60 oz (414 g)
Unit Type of Package 3	CAR
Number of Units in Package 3	1350
Package 3 Height	11.81 in (30 cm)
Package 3 Width	11.02 in (28 cm)

Package 3 Length	15.35 in (39 cm)
Package 3 Weight	28.33 lb(US) (12.852 kg)

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

### Contractual warranty

Warranty	18 months
----------	-----------