

Professional desktop label printer with Wi-Fi

PT-P900Wc

www.brother.eu



Professional PC connectable label printer with integrated Wi-Fi

Create customised, durable labels in many colour combinations and widths with this feature-rich, high-speed label printer. Design labels on your PC, Mac, tablet or smartphone then print using USB or Wi-Fi. Include barcodes, logos and other images, frames and text, and link to existing data in your spreadsheet to easily print many labels at once. Advanced cutter with easy peel feature ensures efficient labelling. Optional rechargeable battery base offers a total mobile labelling solution.

PT-P900Wc



Key features:

- Integrated Wi-Fi to print labels from several devices at once, including tablets and smartphones
- High speed and high resolution printing
- Create durable labels up to 36mm in width
- Advanced cutter with easy label peel function
- Connect to data contained in spreadsheets to batch print many labels at once
- Include images, barcodes and frames on your labels

The professional label printer designed for any labelling task

With a wide range of colour combinations and tape widths up to 36mm, near borderless printing and high speed/high resolution print capabilities, the PT-P900Wc is ideal for facilities management, document archiving, asset labelling and creating on-demand labels whenever and wherever required.

Print from smartphones or tablets

Instantly create and print simple labels from your smartphone or tablet without needing to fire up your PC. The Brother iPrint&Label app wirelessly connects to the PT-P900Wc to let you design and print labels from your iOS or Android device. Or if you need to identify electrical cables and equipment, use the specialised Brother Pro Label Tool app to print labels for wrapping around cables or for sticking to faceplates, electrical distribution boards and other specialist equipment.

General

Carton contents

- PT-P900W Label printer
- 36mm TZe black on white tape cassette (8m)
- AC adapter
- AC power cord
- USB cable
- Documentation

Language support

English, German, French, Dutch, Italian, Spanish, Portuguese, Danish, Norwegian, Swedish, Finnish, Hungarian, Czech, Polish, Romanian, Slovenian, Slovakian, Croatian, Brazilian Portuguese, Turkish

Weights and dimensions

Machine only (W) x (D) x (H)

118mm x 192mm x 146mm

Weight (Kg)

1.48Kg

With Carton (W) x (D) x (H)

165mm x 226mm x 333mm

Weight (Kg)

2.74Kg

Printing

Supported printer commands

ESC/P
P-touch template
Raster

Printing speed

Up to 60mm/second

Print resolution

360dpi

Maximum tape width

36.0mm

Maximum print height

32.0mm

Label length

4mm minimum
1000mm maximum

Maximum lines per label

17

Vertical printing

Yes

Mirror printing

Yes

Copies

1 to 999

Numbering

1 to 999

Cutter type

Automatic full and half-cut

Software & app compatibility

P-touch Editor

PC/Mac

iPrint&LabelApp

iOS/Android

Pro Label Tool App

iOS/Android

Connectivity

USB Interface

Windows®
(USB1.1, 2.0, 3.0 protocol)
Mac
(USB 1.0, 2.0 protocol)

Wi-Fi

Wireless Direct: IEEE802.11n
Infrastructure mode:
IEEE802.11b/g/n
WPS 2.0

Serial

RS-232C (for printing with
ESC/P commands only.
Requires optional serial
adapter cable)

Operating system support

Windows:
Vista, 7, 8, 8.1, 10
Server 2008, 2008 R2, 2012,
2012 R2
Mac:
10.8-10.10

Barcode Symbologies

Supported

CODE39, ITF (I-2/5), EAN-13, EAN-8, UPC-A, UPC-E, CODABAR, CODE128, GS1-128 (UCC/EAN-128), QR Code, PDF417, Data Matrix, MaxiCode, RSS-14 (Standard, Truncated, Stacked, Stacked Omni), RSS-Limited, RSS Expanded (Standard, Stacked), POSTNET, Aztec, MaxiCode

Memory for label template transfer

Flash memory size
6MB

Memory locations
99 areas

Supplies

Tape types
TZe, HSe, FLe

Tape widths
TZe/HGe: 3.5, 6, 9, 12, 18, 24, 36mm
HSe: 5.2, 9.0, 11.2, 21.0, 31.0 mm
FLe: 21mm (width) x 45mm (length)

Optional Accessories

Li-ion battery
PA-BT-4000LI

Serial adapter cable
PA-SCA-001

Battery base
PA-BB-002

AC adapter
AD9100ESA

