



Part Number : [1731110498](#)

Product Description : FCT Plastic Backshell for D-Sub Connector, Black, Shell Size 4, Straight Cable Outlet, with 4-40 UNC Knurled Thumb Screws and 4-40 UNC Locking Screws

Series Number : 173111

Status : Active

Product Category : D-Sub Backshells

Engineering Number : FKH4-4380




Documents & Resources

Drawings

[Drawing 1731110498_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	D-Sub Backshells
Series	173111
Description	FCT Plastic Backshell for D-Sub Connector, Black, Shell Size 4, Straight Cable Outlet, with 4-40 UNC Knurled Thumb Screws and 4-40 UNC Locking Screws
Product Family	FCT D-Sub Connectors
Product Name	FCT Products
Type	Plastic
UPC	191130024872

Electrical

Shield Type	None
Shielded	No

Physical

Cable Diameter	8.00-10.50mm
Color - Resin	Black
Material - Backshell	ABS / PC+ABS
Material - Screw	Brass
Mounting Style	Knurled Thumb Screw Lock
Net Weight	32.900/g
Orientation	Straight
Packaging Type	Tubular Foil
Plating - Backshell	None
Temperature Range - Operating	-35° to +120°C
Thread Size	4-40 UNC
Thread Type	Standard
Tightening Test Torque	40 Ncm

Waterproof / Dustproof	No
------------------------	----

Use with Part(s)

Description	Part Number
Use With	FCT D-Sub, Size 4
