
# Directional DAS Series SISO 4G/5G+UHF Antenna

PD380-4000S1NF





1



### Features & Applications:

- Includes public safety, PMR, TETRA band 380-520MHz
- @ 4G / 5G-FR1 698-4000MHz
- In-building wall mount
- Directional radiation pattern
- Low PIM and SAR compliant
- Connector N-Female as standard
- @ For 4.3-10 Female version use P/N: PD380-4000S143

ELECTRICAL SPECIFICATIONS								
PD380-4000S	S1NF							
Frequency range		MHz	380-520	698-960	1710-2700	3400-4000		
Gain		dBi	4.0±1 5.0±1		7.0±1	7.5±1		
Polarization			Vertical					
Beam width	Horizontal	deg	150	90	75	55		
	Vertical		50	65	65	30		
VSWR			≤2.5	≤2.0	≤2.0	≤2.0		
Front-to-back ratio		dB	>2	>4	>8	>10		
PIM,3rd order,2x20W		dBc	- ≤-140					
Max. input power		W	50					
Impedance		Ohm	50					
SAR compliance			Compliant based on whole-body SAR limit RF Exposure calculation (CEI EN 50383)					

MECHANICAL SPECIFICATIONS									
PD380-4000S1NF									
Dimensio (W x L x I		rsing Color erial		or	Weight	Mounting Kit			
308 x 190 x 6 (12.13 x 7.48 x 2	U	ABS, White			0.6kg (1.323lbs)	Wall mount (standard)			
Wireless Technology	No. of Port		Cable Length			Cable Type		Connector Type	
<b>4G,5G FR1, UHF</b> 1			1.47Ft (0.45m)		Ø 0.160" low loss		NF		

ENVIRONMENTAL SPECIFICATIONS								
PD380-4000S1NF								
Operating Temperature	Storage Temperature	RoHS Compliant	Ingress Protection	Warranty				
-55 / +60° C	-55 / +60° C	Yes	IP50	2 years				

PulseElectronics.com Preliminary: (23/17)


# Directional DAS Series SISO 4G/5G+UHF Antenna

PD380-4000S1NF

Mechanical Drawing



#### PD380-4000S1NF



### **Test Setup**

General / Chamber Setup

2



PulseElectronics.com Preliminary: (23/17)


## **Directional DAS Series** SISO 4G/5G+UHF Antenna PD380-400051NF




### Radiation Pattern - Vertical and Horizontal Plane

#### PD380-4000S1NF

#### Vertical



#### Horizontal



Preliminary: (23/17) PulseElectronics.com

# Directional DAS Series SISO 4G/5G+UHF Antenna

PD380-4000S1NF



#### **PACKAGING**

#### PD380-4000S1NF


1.Inner box: 385\*227\*80mm;

2.Outer box size: 780\*400\*475mm;

3. 20Pcs/Carton;

#### Installation instructions

#### PD380-4000S1NF



#### Notes:

1. Please contact sales for availability, lead time, and/or any special requests. Samples available upon request.

#### For More Information:

Americas - antennas.us@pulseelectronics.com | Europe - antennas.eu@pulseelectronics.com | Asia - antennas.as@pulseelectronics.com | Questions? +1-800-ANTENNA Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright , 2020. Pulse Electronics, Inc. All rights reserved. Company address: Pulse Electronics, a YAGEO Company, 15255 Innovation Drive, Suite #100, San Diego, CA 92128

PulseElectronics.com Preliminary: (23/17)