


Polyethylene Spiral Binding with UL94V0 classification SBPAV0

Due to its excellent flame protection properties, SBPAV0 spiral binding is particularly suitable for the rail and aviation industries as well as public buildings.

Features and benefits

- Organises and protects cables and hoses
- Self-extinguishing according to UL94 V0
- Very good protection against abrasion
- Suitable for retro-fitting
- Cables branch out at any point
- Wide range of diameters



Spiral binding



Spiral binding SBPAVO.

MATERIAL	Polyamide 6 V0 (PA6V0)			
Operating Temperature	-40 °C to +95 °C, intermittent +130 °C			
Flammability	UL 94 V0			
EN 45545-2 Classification	R22 HL2, R23 HL2			



ТҮРЕ	Nominal Ø	Wall (WT)	Pitch (P)	Bundle Ø min.	Bundle Ø max.	Colour	Reel Length	Article-No.
SBPAV01.5	1.5	0.4	6.0	1.6	8	Black (BK)	30 m	161-44000
SBPAV04	4	0.6	7.8	5	20	Black (BK)	30 m	161-44100
SBPAV06	6	0.8	10.0	7.5	40	Black (BK)	30 m	161-44150
SBPAV09	9	1.0	12.5	10	100	Black (BK)	30 m	161-44200
SBPAV016	16	1.2	16.0	20	150	Black (BK)	30 m	161-44300

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content.





For product specific approvals and specifications please refer to the Appendix.

Add items to your watchlist!