

PRODUCT DATA SHEET

Part Number: 2083X23X

Type	Size	Power	Description
Lamp	S25 BA15S	3 W	LED Replacement lamp

S25, BA15S, 39x3014LEDs

Dimensions: mm



Part #	Colour (K)	Voltage (V)*	Nom Current (mA)	Luminous Intensity (Lm)	Life Hrs
20838231	Warm White 2700 – 3000K	10 - 30Vdc	210mA @ 12V	350	30000
20838233	White 6000 – 6500K	10 - 30Vdc	210mA @ 12V	350	30000

Notes:

- * This product is not polarity sensitive.
- RoHS and REACH compliant.
- Due to component tolerances, colour temperature variations may be observed.
- Marking: Operational voltage.
- Electrical & optical data are measured at an ambient temperature of 25°C.