



Part Number : [151200231](#)

Product Description : 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 76.00mm Cable Length, Gold (Au) Plating, 22 Circuits

Series Number : 15120

Status : Active

Product Category : Flexible Printed Circuit (FPC) Flex Jumpers



Documents & Resources

Drawings


[Drawing 151200231_sd.pdf](#)

Specifications

[Product Specification 151200001-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Flexible Printed Circuit (FPC) Flex Jumpers
Series	15120
Description	0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 76.00mm Cable Length, Gold (Au) Plating, 22 Circuits
Product Family	FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Product Name	Premo-Flex FFC Jumper
UPC	196823479540

Electrical

Current - Maximum per Contact	0.35A
Voltage - Maximum	60V AC

Physical

Cable Length	76.00mm
Circuits (Loaded)	22
Contact Layout Type	A (same side)
Material - Outer Jacket	Polyester
Material - Plating Mating	Gold
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	Flat Flex Cable
Wire Size (AWG)	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right- Angle, Top Contact, 2.00mm Height, 22 Circuits, Gold Plating	<u>0524352271</u>
Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right- Angle, Bottom Contact, 2.00mm Height, 22 Circuits, Gold Plating	<u>0524372271</u>
Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Vertical, 3.90mm Height, 22 Circuits, Gold Plating	<u>0525592253</u>
Easy-On FFC/FPC Connector, 0.50mm Pitch, V-Flip Series, Vertical, 4.05mm Height, 22 Circuits, Phosphor Bronze, Gold Plating	<u>5019512230</u>
Easy-On FFC/FPC Connector, 0.50mm Pitch, FBH1 Series, Right- Angle, Dual Contact, 1.00mm Height, 22 Circuits, Gold over Nickel Plating	<u>5034802200</u>
Easy-On FFC/FPC Connector 0.50mm Pitch, FD19 Series, Right- Angle, Bottom Contact, 1.90mm Height, 22 Circuits, Gold over Nickel Plating	<u>5051102291</u>