

7m (23ft) DisplayPort Cable - 2560 x 1440p - DisplayPort to DisplayPort Cable - DP to DP Cable for Monitor - DP Video/Display Cord - Latching DP Connectors - HDCP & DPCP

Product ID: DISPL7M



The DISPL7M DisplayPort Cable with latches provides a secure connection between your DisplayPort-enabled devices and allows for a connection distance of up to 7 meters between your source and display.

With a bandwidth of 10.8Gbps and support for maximum resolutions up to 2560x1600 (WQXGA), as well as optional audio support, this 7-meter DisplayPort cable offers impressive video capability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

The DISPL7M is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connecting a DisplayPort display to a PC or other DisplayPort source

Features

- **HIGH PERFORMANCE CABLE:** This 7m (23ft) DisplayPort to DisplayPort cable supports 2K (2560x1440p) 30Hz, Full HD (1920x1200p) 60Hz, 10.8 Gbps bandwidth, Multi-Stream Transport (MST), 5.1, 7.1 Audio Channel, GTC for precise audio channel timing & 3D Stereo

- **RELIABLE DESIGN:** Durable ABS connectors with flexible PVC strain relief & jacket prevents fraying/damage due to bending or rough usage; Metal connector sub-structure provides EMI shielding; Latching DP connectors prevent accidental disconnection
- **QUALITY CONSTRUCTION:** 26AWG wire with gold-plated connectors for improved signal integrity and reliability; Superior EMI shielding with Al-Mylar foil and copper braid provides higher quality video and audio; Backwards compatible with DP 1.1
- **APPLICATIONS:** Ideal for home/offices/boardrooms/conference rooms/classrooms; works with your professional workstations with FirePro S9000/7000, W8100/7100/5100 or R5000 graphic cards; Use with 1080p/UHD/4K monitors, projector or large display
- **SPECS:** 7 m (23 ft) Black DisplayPort v1.0 DP Latching Male to Male 26 AWG PVC cable jacket, ABS connector shell Shield: Al-Mylar foil with Braid Protocols: MST, GTC Lifetime Warranty

Hardware

| | |
|-----------------------|--------------------------------|
| Warranty | Lifetime |
| Connector Plating | Nickel |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |
| Fire Rating | CMG Rated (General Purpose) |

Connector(s)

| | |
|-------------|--------------------------|
| Connector A | 1 - DisplayPort (20 pin) |
| Connector B | 1 - DisplayPort (20 pin) |

Physical Characteristics

| | |
|-------------------|-------------------|
| Color | Black |
| Connector Style | Latching |
| Wire Gauge | 26 AWG (0.404 mm) |
| Cable Length | 23.0 ft [7 m] |
| Product Length | 23.0 ft [7.0 m] |
| Product Width | 0.8 in [2.0 cm] |
| Product Height | 0.6 in [1.4 cm] |
| Weight of Product | 1.1 lb [0.5 kg] |

**Packaging
Information**

| | |
|------------------------------|-------------------|
| Package Quantity | 1 |
| Package Length | 12.8 in [32.5 cm] |
| Package Width | 9.8 in [25.0 cm] |
| Package Height | 1.6 in [4.1 cm] |
| Shipping (Package) Weight | 1.2 lb [0.5 kg] |

What's in the Box

| | |
|---------------------|---|
| Included in Package | 1 - 7m DisplayPort Cable with Latches - M/M |
|---------------------|---|

****Product appearance and specifications are subject to change without notice.***