

## 6in DVI-D Dual Link Digital Port Saver Extension Cable M/F

**Product ID:** DVIDEXTAA6IN



The DVIDEXTAA6IN 6-inch DVI-D Port Saver Cable/coupler avoids expensive repairs to a computer or display. It does this by extending the port by 6in, thereby eliminating the weight and stress that would typically be placed on the port by a DVI cable. This is especially useful in an environment where cables are unplugged and re-inserted frequently.

The 6in DVI-D cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Extend a video card or monitor DVI-D port by 6in, to protect against damage from frequent connect/disconnects

### Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec

- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

---

#### Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

#### Connector(s)

Connector A	1 - DVI-D (25 pin)
Connector B	1 - DVI-D (25 pin)

---

#### Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	0.5 ft [0.2 m]
Product Length	6.0 in [152.4 mm]
Product Width	1.6 in [40 mm]
Product Height	0.6 in [1.6 cm]
Weight of Product	2.8 oz [79 g]

---

#### Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.6 in [16 mm]
Shipping (Package) Weight	3.0 oz [84 g]

---

**What's in the Box**

Included in Package

1 - 6in DVI-D Dual Link Digital Port Saver Cable M/F

---

*\*Product appearance and specifications are subject to change without notice.*