

## 3m DVI-D Single Link Cable - M/M

**Product ID:** DVIDSMM3M



The DVIDSMM3M DVI-D Single Link cable features 2 male DVI (19-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 3m DVI-D male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Connect your desktop or laptop computer to a DVI-D Single Link display or projector

### Features

- Supports resolutions up to 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Aluminum-mylar foil with braided shielding

- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

---

**Hardware**

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Industry Standards	DVI DDWG Standard

---

**Connector(s)**

Connector A	1 - DVI-D (19 pin)
Connector B	1 - DVI-D (19 pin)

---

**Physical Characteristics**

Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	9.8 ft [3 m]
Product Length	9.8 ft [3.0 m]
Product Width	1.6 in [4.0 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	10.0 oz [283.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	1.5 in [3.7 cm]

Shipping (Package) Weight	10.3 oz [293.0 g]
------------------------------	-------------------

---

**What's in the Box**

Included in Package	1 - 3m DVI-D Single Link Cable - M/M
---------------------	--------------------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

