

20 ft DVI-I Dual Link Digital Analog Monitor Cable M/M

Product ID: DVIIDMM20



The DVIIDMM20 DVI-I Dual Link cable features 2 male DVI-I (29-pin) connectors and offers 20 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-I monitor or projector.

The 20ft DVI-I male to male cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect your desktop or laptop computer to a DVI-I Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference

- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards
- Supports both analog and digital displays

Hardware

Warranty	Lifetime
Industry Standards	DVI DDWG Standard

Performance

Maximum Data Transfer Rate	9.9 Gbits/sec
----------------------------	---------------

Connector(s)

Connector A	1 - DVI-I (29 pin)
Connector B	1 - DVI-I (29 pin)

Physical Characteristics

Color	Black
Wire Gauge	28/30 AWG
Cable Length	20.0 ft [6.1 m]
Product Length	20.0 ft [6.1 m]
Weight of Product	26.7 oz [757 g]

Packaging Information

Package Quantity	1
Package Length	13.0 in [33 cm]
Package Width	10.0 in [25.5 cm]
Package Height	2.0 in [50 mm]
Shipping (Package) Weight	27.3 oz [774 g]

What's in the Box

Included in Package 1 - 20 ft Dual Link Digital Analog Monitor DVI-I Cable - M/M

****Product appearance and specifications are subject to change without notice.***