


12in Latching SATA to Right Angle SATA Serial ATA Cable

Product ID: LSATA12RA1



This 12in right-angled latching SATA cable features a (straight) female Serial ATA connector as well as a right-angled (female) SATA connector, providing a simple connection to a Serial ATA drive even if space near the drive's SATA port is limited. The cable offers latching connectors, which ensure secure connections for SATA hard drives and motherboards that support this feature.

Once the right-angled SATA connector has been inserted into the drive's SATA data port, the shaft of the cable is seated flush with the rear panel of the drive, eliminating the clutter of excess cable at the connection point - an ideal solution for small or micro form factor computer cases.

The right angled SATA cable supports high speed data transfers up to 6Gbps, and features a thin, narrow construction that helps to improve airflow within the computer case; the cable features a rugged, yet flexible design that makes it easy to make the SATA connection as needed, and is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

Features

- Compliant with Serial ATA III Specifications
Fast data transfer rate of up to 6 Gbps

Performance

Warranty	Lifetime
Type and Rate	SATA III (6 Gbps)

Connector(s)

Connector A	1 - SATA (7 pin, Data)
Connector B	1 - SATA (7 pin, Data)

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	0-95%

Physical Characteristics

Color	Red
Connector Style	Straight to Right Angle
Cable Length	12.0 in [304.8 mm]
Product Length	12.0 in [30.5 cm]
Product Width	0.6 in [1.4 cm]
Product Height	0.2 in [6.0 mm]
Weight of Product	0.3 oz [8.0 g]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.3 in [7.0 mm]
Shipping (Package) Weight	0.5 oz [13.0 g]

What's in the Box

Included in Package	1 - 12in SATA to Right Angle SATA Serial ATA Cable
---------------------	----------------------------------------------------

****Product appearance and specifications are subject to change without notice.***