

4 Port Black USB 2.0 Hub

Product ID: ST4202USBGB



This TAA compliant 4 Port USB 2.0 Hub connects to one USB 2.0 port on a Mac or PC computer, adding four USB 2.0 ports - allowing you to maximize the number of high speed USB peripherals connected to your computer. The hub supports cascaded installation with other USB 2.0 hubs, supporting up to 127 USB 2.0 device connections - a scalable solution for connecting multiple USB devices to a single host computer.

The 4 port hub includes a power adapter, but can be powered through USB bus connection to the host computer - allowing you to install the hub as needed without worrying about the availability of a power outlet.

The USB 2.0 hub offers an attractive black casing that suits any operating environment and includes a 3ft USB 2.0 A/B male-male cable, for the connection between the hub and the host computer.

Certifications, Reports and Compatibility



Applications

- Charge iPod's or portable devices that can be recharged through USB 2.0
- Connect USB cameras, printers, MP3 Players, and more

Features

- TAA Compliant
- Choice of Bus Power and/or External Power Adapter
- Compact space saving design
- Hot Plug and Play feature allows devices to be connected or disconnected without turning off the PC
- Maximum data transfer rate of up to 480 Mbps and backwards compatible with USB 1.1
- Quick, easy installation

Hardware

Warranty	2 Years
Ports	4
Interface	USB 2.0
Industry Standards	USB 2.0

Performance

Maximum Data Transfer Rate	480 Mbps
----------------------------	----------

Connector(s)

External Ports	4 - USB 2.0 Type-A (4 pin, 480Mbps)
	1 - USB B (4 pin)

Software

OS Compatibility	OS Independent; No additional drivers or software required
------------------	--

Special Notes / Requirements

System and Cable Requirements	Any computer with a USB 2.0 port
-------------------------------	----------------------------------

Indicators

LED Indicators	1 - Power
----------------	-----------

Power

Power Source	AC Adapter Included
--------------	---------------------

Input Voltage	100 - 240 AC
Input Current	0.35 A
Output Voltage	5 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	H
Power Consumption (In Watts)	10

Environmental

Operating Temperature	0 to 70 Degrees C
-----------------------	-------------------

Physical Characteristics

Color	Black
Material	Plastic
Product Length	3.9 in [10 cm]
Product Width	2.4 in [60 mm]
Product Height	0.8 in [2 cm]
Weight of Product	10.0 oz [284 g]

Packaging Information

Package Quantity	1
Package Length	6.0 in [15.2 cm]
Package Width	3.7 in [95 mm]
Package Height	10.2 in [26 cm]
Shipping (Package) Weight	0.7 lb [0.3 kg]

What's in the Box

Included in Package	1 - 4 Port USB 2.0 Hub
	1 - USB Cable

1 - Power Adapter (UK)

1 - Instruction Manual

****Product appearance and specifications are subject to change without notice.***