

2m USB 2.0 A to A Cable - M/M

Product ID: USB2AA2M



The USB2AA2M 2-meter USB 2.0 cable features two USB 'A' male connectors, delivering a dependable way to connect your PC to a USB hub, or connect USB 2.0 peripherals to a USB hub.

Fully rated to USB 2.0 performance specifications, this high quality USB cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connecting USB 2.0 devices to a USB hub
- Connecting USB 2.0 devices directly to a computer
- Replace worn-out or misplaced USB cables with this high quality, 2m USB 2.0 A to A, M/M Cable

Features

- Supports USB 2.0 data transfer rates up to 480 Mbps
- Backward compatible with USB 1.1
- High quality USB 'A' male connectors

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Connector(s)

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB 2.0 Type-A (4 pin, 480Mbps)

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	0~95% RH

Physical Characteristics

Color	Black
Wire Gauge	24/28 AWG
Cable Length	6.6 ft [2 m]
Product Length	6.6 ft [2.0 m]
Product Width	0.5 in [1.2 cm]
Product Height	0.3 in [8.0 mm]
Weight of Product	2.7 oz [76.5 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.2 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.4 in [1.0 cm]
Shipping (Package)	2.7 oz [77.5 g]

Weight

What's in the Box

Included in Package	1 - 2 m USB 2.0 A to A Cable - M/M
---------------------	------------------------------------

****Product appearance and specifications are subject to change without notice.***

