

20m USB 2.0 Active Extension Cable - M/F

**Product ID:** USB2AAEXT20M



The USB2AAEXT20M 20m Active USB 2.0 Extension Cable offers one USB-A male connector and one USB-A female connector, and provides an active extension of USB 2.0 devices of up to 20-meters (66-feet).

An all-in-one cable for overcoming distance restrictions as well as power source limitations, the active USB 2.0 extension cable incorporates bus-powered active circuitry to ensure performance beyond the length limits of standard USB cables. Plus you can daisy chain 2 cables for a total USB extension of up to 40-meters.

If necessary, the USB device can be powered from a wall outlet using the Universal AC power adapter (provided with the cable).

The USB2AAEXT20M repeater cable supports the full USB 2.0 bandwidth of 480 Mbps, and is backed by StarTech.com's 2-year Warranty.

## Certifications, Reports and Compatibility



## Applications

- Extend the distance of USB peripherals beyond the USB 2.0 5-meter limitation
- Daisy chain 2 cables together for even longer USB extensions

## Features

- USB bus-powered
- Universal external power source also included
- Blue LED indicator x1 for Extension Cable and USB port connection status monitoring
- Fully shielded for error-free connections
- Plug-and-play, no driver required
- Compatible with PC Windows 8/7/Vista/XP and Mac computer systems

---

**Hardware**

|                       |                          |
|-----------------------|--------------------------|
| Warranty              | 2 Years                  |
| Connector Plating     | Nickel                   |
| Cable Jacket Material | PVC - Polyvinyl Chloride |

---

**Connector(s)**

|             |                                     |
|-------------|-------------------------------------|
| Connector A | 1 - USB 2.0 Type-A (4 pin, 480Mbps) |
| Connector B | 1 - USB 2.0 Type-A (4 pin, 480Mbps) |

---

**Special Notes / Requirements**

|      |   |
|------|---|
| Note | Cascade two USB2AAEXT20M devices together for further extension |
|------|---|

---

**Power**

|                              |                     |
|------------------------------|---------------------|
| Power Source                 | AC Adapter Included |
| Input Voltage                | 100 - 240 AC        |
| Input Current                | 0.35 A              |
| Output Voltage               | 5 DC                |
| Output Current               | 1A                  |
| Center Tip Polarity          | Positive            |
| Plug Type                    | H                   |
| Power Consumption (In Watts) | 5                   |

---

**Environmental**

|                       |                           |
|-----------------------|---------------------------|
| Operating Temperature | 0C to 70C (32F to 122F)   |
| Storage Temperature   | -20C to 85C (-4F to 185F) |

---

**Physical Characteristics**

|                   |                  |
|-------------------|------------------|
| Color             | Black            |
| Cable Length      | 65.6 ft [20 m]   |
| Product Length    | 65.6 ft [20.0 m] |
| Product Width     | 0.6 in [1.6 cm]  |
| Product Height    | 0.4 in [1.0 cm]  |
| Weight of Product | 1.9 lb [0.9 kg]  |

---

**Packaging Information**

|                           |                  |
|---------------------------|------------------|
| Package Quantity          | 1                |
| Package Length            | 6.8 in [17.2 cm] |
| Package Width             | 5.8 in [14.8 cm] |
| Package Height            | 4.8 in [12.2 cm] |
| Shipping (Package) Weight | 2.2 lb [1.0 kg]  |

---

**What's in the Box**

|                     |  |
|---------------------|--|
| Included in Package | 1 - 20 m USB 2.0 Active Extension Cable - M/F                  |
|                     | 1 - Universal Power Adapter                                    |
|                     | 1 - Plug Adapters for North America, UK, Europe, and Australia |

---

***\*Product appearance and specifications are subject to change without notice.***