

USB to USB-C Cable - M/M - 1 m (3 ft.) - USB 3.0 (5Gbps) - USB-A to USB-C

Product ID: USB315AC1M



This USB to USB-C cable lets you connect your USB 3.2 Gen 1, USB Type-C devices such as a hard drive, or mobile device to the USB Type-A port on your computer, charger or tablet.

The USB315AC1M from StarTech.com comes with a 2-year warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Connect USB-C peripherals, such as a hard drive, to your USB-A laptop or tablet
- Charge your USB-C mobile device from a USB-A laptop or wall charger
- Sync your USB-C mobile device with a USB-A computer

Features

- Supports data transfer rates up to 5Gbps (USB 3.2 Gen 1)
 - Guaranteed reliability with our 2-year warranty
-

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 3.0 - 5 Gbit/s
---------------	--------------------

Connector(s)

Connector A	1 - USB Type-A (9 pin, 5 Gbps)
Connector B	1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps)

Environmental

Operating Temperature	0C to 35C (32F to 95F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	5%-80% RH (no condensation)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	24/32 AWG
Cable Length	3.3 ft [1 m]
Product Length	3.3 ft [1.0 m]
Product Width	0.6 in [1.6 cm]
Product Height	0.3 in [8.0 mm]
Weight of Product	1.4 oz [41.0 g]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]

Package Width	4.9 in [12.5 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	1.7 oz [49.0 g]

What's in the Box

Included in Package	1 - USB-C to USB-A cable
---------------------	--------------------------

****Product appearance and specifications are subject to change without notice.***