

1m White USB 2.0 Extension Cable A to A - M/F

Product ID: USBEXTPAA1MW



The USBEXTPAA1MW 1m White USB 2.0 Extension Cable features a USB 'A' male connector and a USB 'A' female connector, enabling you to extend the connection distance between your USB 2.0 devices by up to 1-meter – allowing for better placement of your peripheral devices, or adding flexibility to your existing USB ports.

The cable features thin USB connector moldings which allow you to simplify your connections, and plug into tight fitting locations.

Designed and constructed for maximum durability, this high quality USB 2.0 extension cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Extend the length of your USB 2.0 A to B cable by up to 1m – for convenient placing of your USB 2.0 peripherals

Features

- 1x USB 'A' male connector
- 1x USB 'A' female connector
- Thin USB 2.0 connector moldings, with strain relief

- All white construction
- Supports high-speed data transfer rates of up to 480 Mbps

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Drain

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB 2.0 Type-A (4 pin, 480Mbps)

Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-10C to 30C (14F to 86F)
Humidity	30%-75% RH

Physical Characteristics

Color	White
Connector Style	Straight
Wire Gauge	24/28 AWG
Cable Length	3.3 ft [1 m]
Product Length	3.3 ft [1.0 m]
Product Width	0.5 in [1.2 cm]
Product Height	0.3 in [8.0 mm]
Weight of Product	0.7 oz [19.3 g]

**Packaging
Information**

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	0.9 oz [24.8 g]

What's in the Box

Included in Package	1 - 1m White USB Extension Cable - A to A M/F
---------------------	---

****Product appearance and specifications are subject to change without notice.***