

## 1 ft VGA to 2x VGA Video Splitter Cable – M/F

**Product ID:** VGASPL1VV



This VGASPL1VV 1-foot VGA video splitter cable lets you connect two VGA displays to a single VGA video source.

A cost-effective solution for dual VGA monitor configurations, this high-quality splitter cable is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Easily enable one VGA signal to be connected to two displays
- Drive two displays from one source using just a cable

### Features

- Split a single VGA signal into two
- No power adapter required

---

#### Hardware

Warranty

Lifetime

Number of Conductors	15
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)

---

#### Performance

Maximum Digital Resolutions	20481536 @ 85Hz
-----------------------------	-----------------

---

#### Connector(s)

Connector A	1 - VGA (15 pin, High Density D-Sub)
Connector B	2 - VGA (15 pin, High Density D-Sub)

---

#### Special Notes / Requirements

Note	This product will split your video signal to deliver two identical images of the same resolution. It cannot be used to span an image across two displays, or to show different images on each display.
------	--

---

#### Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Max Connector Dimension	1.6 in [41 mm]
Cable Length	1.0 ft [0.3 m]
Cable OD	0.4 in [9.0 mm]
Product Length	12.0 in [30.5 cm]
Product Width	1.6 in [4.1 cm]
Product Height	1.5 in [3.7 cm]
Weight of Product	5.6 oz [159.0 g]

---

#### Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	1.5 in [3.8 cm]
Shipping (Package) Weight	5.8 oz [164.0 g]

---

**What's in the Box**

Included in Package	1 - 1 ft VGA to 2x VGA Video Splitter Cable – M/F
---------------------	---

---

***\*Product appearance and specifications are subject to change without notice.***