

Composite and S-Video to HDMI Converter with Audio

Product ID: VID2HDCON



The VID2HDCON Composite and S-Video to HDMI Video Converter (with Audio) lets you connect an S-Video or Composite device, along with supporting 3.5mm audio, to your HDMI monitor or television.

Equipped with convenient selector switches for easy configuration, the S-Video/Composite to HDMI converter is able to function with both NTSC and PAL systems, and offers support for output resolutions up to 1600x1200 (PC) or 1080p (TV) to seamlessly integrate with almost any display.

The converter features an integrated 3.5mm audio connection that enables sending the output through a single HDMI cable to your destination display, avoiding the hassle of running a separate audio cable.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Convert VCRs, DVD players, camcorders, video game consoles and other home theater devices to work on HDMI displays

Features

- Functions with NTSC and PAL systems

- PC/TV resolution selector switch for compatibility with many different displays
- 50/60 Hz frame rate conversion
- On Screen Display
- Plug and play installation - no software/drivers required
- Advance 3D motion adaptive de-interlace
- 3D (frame based) motion adaptive YNR/CNR noise reduction

Hardware

| | |
|---------------------------|---|
| Warranty | 2 Years |
| Active or Passive Adapter | Active |
| AV Input | Composite S-Video 3.5 mm Stereo Audio |
| AV Output | HDMI |
| Audio | Yes |
| Industry Standards | NTSC 3.58 and PAL |

Performance

| | |
|-----------------------|---|
| Supported Resolutions | PC - 1600x1200, 1280x1024, 1024x768 TV - 1080p, 720p, 576p, 480p |
|-----------------------|---|

Connector(s)

| | |
|-------------------|--|
| Connector Type(s) | 1 - Composite Video (1 x RCA) 1 - S-Video (4 pin, Mini-DIN) 1 - HDMI (19 pin) 1 - 3.5 mm Mini-Jack (3 Position) |
|-------------------|--|

Indicators

| | |
|----------------|---|
| LED Indicators | 1 - Red - S-Video, Yellow - Composite Video |
|----------------|---|

Power

| | |
|--------------|---------------------|
| Power Source | AC Adapter Included |
|--------------|---------------------|

| | |
|------------------------------|--------------|
| Input Voltage | 100 - 240 AC |
| Input Current | 0.3A |
| Output Voltage | 5 DC |
| Output Current | 1.2A |
| Center Tip Polarity | Positive |
| Plug Type | M |
| Power Consumption (In Watts) | 2.5 |

Environmental

| | |
|-----------------------|---------------------------|
| Operating Temperature | 0C to 40C (32F to 104F) |
| Storage Temperature | -20C to 60C (-4F to 140F) |
| Humidity | 20~90% RH |

Physical Characteristics

| | |
|-------------------|------------------|
| Color | Black |
| Material | Plastic |
| Product Length | 3.9 in [10.0 cm] |
| Product Width | 2.5 in [6.4 cm] |
| Product Height | 1.0 in [2.5 cm] |
| Weight of Product | 3.0 oz [84.0 g] |

Packaging Information

| | |
|---------------------------|-------------------|
| Package Quantity | 1 |
| Package Length | 4.9 in [12.4 cm] |
| Package Width | 6.1 in [15.5 cm] |
| Package Height | 2.2 in [5.6 cm] |
| Shipping (Package) Weight | 10.9 oz [310.0 g] |

What's in the Box

| | |
|---------------------|--|
| Included in Package | 1 - Composite/S-Video to HDMI Converter |
| | 1 - Universal Power Adapter (NA/JP, EU, UK, ANZ) |
| | 1 - Instruction Manual |

****Product appearance and specifications are subject to change without notice.***