

## Product information

# 97 52 14

### Crimping Pliers

Short design




- Available as accessory: locator for non-insulated open plug-type connectors
- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling due to 20° angled head, low weight and short design
- Crimping die is not exchangeable
- Special quality chrome vanadium electric steel, oil-hardened

### General

Article No.	97 52 14
EAN	4003773026808
Pliers	burnished
Head	burnished
Handles	with multi-component grips
Weight	387 g
Dimensions	195 x 77 x 22 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

### Technical details



Application	non-insulated open plug type connectors (plug width 2.8 + 4.8 mm)
Capacity in square millimetres	0.1 — 1.5 mm <sup>2</sup>
Number of crimping positions	4
AWG	26 — 16

### Accessories

97 59 14	Locator for 97 52 14,
----------	-----------------------

*technical change and errors excepted*

