

Product information

97 81 180

- For crimping wire ferrules according to DIN 46228 parts 1 + 4 in the range 0.5 to 6 mm²
- Ideal for work in confined areas, e.g. in narrow and deep switch boxes
- Special tool steel, forged, oil-hardened

Crimping Pliers for wire ferrules


With front loading



General

Article No.	97 81 180
EAN	4003773019794
Head	polished
Handles	plastic coated
Weight	209 g
Dimensions	180 x 50 x 13 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details



Application	Wire ferrules
Capacity in square millimetres	0.5 — 6.0 mm ²
Number of crimping positions	1
AWG	20 — 10

technical change and errors excepted

