

Product information

48 21 J31

Precision Circlip Pliers

For internal circlips in bore holes

DIN 5256 D



O<u>√90</u>°

- Heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- With inserted tips for reliable work
- · Bolted joint: precise, zero backlash operation of pliers
- Non-slip plastic coating on the handles
- DIN 5256 D; 90° angled jaws
- Inserted tips: spring steel wire, drawn
- Pliers body: chrome vanadium electric steel, forged, oil-hardened



General	
Article No.	48 21 J31
EAN	4003773048657
Pliers	grey atramentized
Handles	with non-slip plastic coating
Weight	265 g
Dimensions	210 x 45 x 13 mm
Standard	DIN 5256 D
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Size of bore	Ø 40 – 100 mm
Tips (diameter)	Ø 2.3 mm

technical change and errors excepted