

## Product information

# 48 21 J41


## Precision Circlip Pliers

For internal circlips in bore holes

DIN 5256 D

- Heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- With inserted tips for reliable work
- Bolted joint: precise, zero backlash operation of pliers
- Non-slip plastic coating on the handles
- DIN 5256 D; 90° angled jaws
- Inserted tips: spring steel wire, drawn
- Pliers body: chrome vanadium electric steel, forged, oil-hardened



 90°



### General

Article No.	48 21 J41
EAN	4003773048664
Pliers	grey atramentized
Handles	with non-slip plastic coating
Weight	576 g
Dimensions	305 x 45 x 17 mm
Standard	DIN 5256 D
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Size of bore	Ø 85 – 140 mm
Tips (diameter)	Ø 3.2 mm

*technical change and errors excepted*