

## Product information

# 49 21 A41

## Precision Circlip Pliers

For external circlips on shafts

DIN 5254 B



- Heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- With inserted tips for reliable work
- Large contact faces on the tips: no distortion of circlips, easy fitting
- Bolted joint: precise, zero backlash operation of pliers
- Internal opening spring, protected and captive
- Non-slip plastic coating on the handles
- DIN 5254 B; 90° angled jaws
- Inserted tips: spring steel wire, drawn
- Pliers body: chrome vanadium electric steel, forged, oil-hardened

MM  $\angle 90^\circ$



| General         |                               |
|-----------------|-------------------------------|
| Article No.     | 49 21 A41                     |
| EAN             | 4003773048855                 |
| Pliers          | grey atramentized             |
| Handles         | with non-slip plastic coating |
| Weight          | 601 g                         |
| Dimensions      | 305 x 56 x 28 mm              |
| Standard        | DIN 5254 B                    |
| REACH compliant | does not contain SVHC         |
| RoHS compliant  | not applicable                |

| Technical details |               |
|-------------------|---------------|
| Size of shaft     | Ø 85 – 140 mm |
| Tips (diameter)   | 3.2 mm        |

*technical change and errors excepted*





Spring inside the joint: the spring is protected inside the precisely bolted joint. It does not hinder work and cannot get dirty or lost.