

Product information

36 12 130

Electronics Mounting Pliers



- To bend wire in shape for the distance to the board
- Precision pliers for very fine assembly and repair work in electronics
- For bending and cutting off wire ends on components
- Sturdy, zero backlash box joint
- Smooth ground gripping surfaces
- Edges carefully deburred
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Ball bearing chrome steel, oil hardened

W

General

Article No.	36 12 130
EAN	4003773016861
Head	mirror polished
Handles	with multi-component grips
Weight	70 g
Dimensions	130 x 68 x 17 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Jaw thickness (joint) (T1)	9.5 mm
Tips thickness (W4)	6.0 mm
Head width (W3)	12.0 mm
Handle width	5.5 mm
Jaw length (L3)	23.0 mm
Application	bend wire shape

technical change and errors excepted

