

Product information

83 30 020

Pipe Wrench S-Type

DIN 5234

- Slim, S-type jaw
- Jaws with offset teeth in opposite direction
- Teeth additionally induction-hardened
- Three-point contact on pipes, self-locking
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Gripping jaws with specially hardened teeth, hardness approx. 56 HRC
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General

Article No.	83 30 020
EAN	4003773014263
Pliers	red powder-coated
Weight	2,669 g
Dimensions	570 x 95 x 26 mm
Standard	DIN 5234
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Clamping width	70 mm
Capacities for pipes (diameter)	Ø 2 3/4 Inch
Capacities for pipes (diameter)	Ø 70 mm
Capacities for nuts	70 mm
Inner diameter, inches	Ø 2 Inch

technical change and errors excepted

