



**Part Number :** [936010129](#)

**Product Description :** GWconnect Screw Terminal Insert, Female, 4-Pole, 10A, without Wire Protection, Silver (Ag) Plated Contacts, Size 3A «21x21»

**Series Number :** 93601

**Status :** Active

**Product Category :** Heavy-Duty Connectors

**Engineering Number :** 7204.6002.0



---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c); 6(c); 6(c) per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

## General

Status	Active
Category	Heavy-Duty Connectors
Series	93601
Description	GWconnect Screw Terminal Insert, Female, 4-Pole, 10A, without Wire Protection, Silver (Ag) Plated Contacts, Size 3A «21x21»
Component Type	Inserts - Screw Terminal
Insert Series	S-A3/4
Product Family	GWconnect Heavy Duty Connectors (HDC)
Product Name	GWconnect
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC	887191871974

## Agency

CSA	256883
UL	E249674

## Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	230V / 400V
Wire Protection	No

## Physical

Component Size	3A «21x21»
Durability (mating cycles max)	500
Gender	Female
Insert Color	Grey
Material - Contact	Copper Alloy
Material - Insert	Polycarbonate
Material - Plating	Silver
Net Weight	13.100/g
Number of Rows	2

Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	4
Stripping Length	6.00mm
Temperature Range - Operating	-40° to +125°C
Tightening Test Torque	0.25 Nm
Wire Size (AWG)	14-20
Wire Size mm <sup>2</sup>	0.50-2.50

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
GWconnect Screw Terminal Insert, Male, 4-Pole, 10A, without Wire Protection, Silver (Ag) Plated Contacts, Size 3A «21x21»	<u>0936010133</u>

### Use with Part(s)

Description	Part Number
Use With	Size 3A «21x21» Hoods and Housings