
Block & Bleed, Soft Seat



Flow Schematic



2170 SERIES

- Combines isolating and venting in a single valve, eliminating the need for tubing and fittings
- Block valve isolates the downstream process fluids and the bleed valve exhausts upstream fluids enabling instruments to be removed without disturbing the permanent piping installation
- The 1/4" NPT vent plug is located 90° to the left and may be removed and replaced with exhaust piping to direct the fluids to a safe location
- 100% helium leak tested to 1 x 10⁻⁴ ml/s for performance and reliability
- Replaceable Delrin[®] seat, and straight through porting for bidirectional, high capacity flow and easy roddable cleaning
- PCTFE or PEEK soft seat optional
- Blow-out proof stem provides a secondary stem seal in the full open position
- FKM o-ring seal and PTFE back-up ring below the stem threads to protect from corrosion and galling; PTFE packing optional
- · All stem threads are rolled for strength and ease of operation
- One-piece bonnet with a metal-to-metal seal to the valve body below the bonnet threads
- · Slotted spring pin to prevent accidental loosening
- Vinyl dust cap for bonnet and stem (non-packing)

SPECIFICATIONS					
Zinc-Nickel plated Steel, electropolished 316 Stainless Steel*					
1/2" & 1/4" NPT Male-female & Female-female configurations available, right venting optional					
6,000 psi @ 200 °F					
0.187"					
C _V 0.76					
All 316 Stainless Steel stems with FKM o-ring and PTFE back-up ring below the threads, PTFE packing optional					
4" standard and 5-3/8" extended length available					
Panel mountings, o-ring materials, handles, packings, regulating stem and stem tips					
Approximately 2.0 lb., extended model 2.7 lb.					

^{*} All 316SS products meet the requirements of NACE MR0175/ISO 15156-3.

For NOSHOK Valves with Steel valve types:



WARNING: This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


For NOSHOK Valves with Stainless Steel valve types:



WARNING: This product can expose you to chemicals including Chromium (VI) and Nickel, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

ORDERING INFORMATION											
SERIES	2	2-valve									
SEAT	1	Soft seat									
PROCESS TYPE	7	Block & bleed									
CONNECTION SIZES	0	1/2" NPT	2	1/4" NPT							
VALVE TYPES	MFC	Male-Female, Steel	FMC	Female-Male, Steel	FFCR	Female-Female, Steel, Right Vent					
	MFCR	Male-Female, Steel, Right Vent	EFMC	Extended Female-Male, Steel	EFFC	Extended Female-Female, Steel					
	EMFC	Extended Male-Female, Steel	FMS	Female-Male, Stainless Steel	FFS	Female-Female, Stainless Steel					
	MFS	Male-Female, Stainless Steel	EFMS	Extended Female-Male, Stainless Steel	FFSR	Female-Female, Stainless Steel, Right Vent					
	MFSR	Male-Female, Stainless Steel, Right Vent	FFC	Female-Female, Steel	EFFS	Extended Female-Female, Stainless Steel					
	EMFS	Extended Male-Female, Stainless Steel									

Please consult your local NOSHOK Distributor or NOSHOK, Inc. for availability and delivery information.



To meet all of your specific application requirements, the following **additional options** are available for these needle valves. To order all or any of these options, simply add them to the part number as shown in the diagram below.


NOTE 1: The example shown includes ALL possible additional options. Please include ONLY the options required for your application when building your part number. (EXAMPLE: 2170-FFC-PK1)

NOTE 2: When a packing option is selected, an o-ring option is NOT available.

ORDERING INFORMATION - ADDITIONAL OPTIONS									
SOFT SEATS	PK1	PEEK	KF1	PCTFE					
PACKING	P1	PTFE							
STEM TIP	T1	Non-rotating (316 Stainless, Isolation Valve Only)							
O-RINGS*	EM1	EPDM	KZ1	FFKM (Kalrez® 3018 or equivalent)	NB1	NBR			
HANDLES	HL1	1-13/16" Mini "T"	HL3	1" Round knurled	HL5	1-3/4" Phenolic			
	HL2	2-1/2" "T"	HL4	1-3/8" Phenolic					


Please consult your local NOSHOK Distributor or NOSHOK, Inc. for availability and delivery information.

Please note that the standard o-ring in all the NOSHOK valves is FKM and the standard handles are block "T" handles (HL2) and bleed 1-3/8" mini "T" handle (HL7). The handle material will always match the material of the valve, unless otherwise specified. For example, the "T" handle (HL2) on the 2170-FFC will be Steel. When only the standard configuration is needed, no additional designations are necessary. Please consult the factory for special application requests.




^{*} Other o-ring materials available on request.

Dimensions




Extended Male-Female




For panel mount, packing, & stem tip dimensions, see pgs. 64-67.

Block & Bleed, Soft Seat

Option With Packing





- 1 Soft tip packing stem and valve packing stem
- 2 Mini valve packing bonnet and valve packing bonnet
- 3 Packing washer
- 4 Packing
- 5 Packing washer
- 6 Jam nut
- 7 Packing adjustment screw