



infrastructure for a connected world

PRODUCT CHANGE NOTIFICATION

Product Category ABRASION PROTECTION **20230921-1**

Product Group DUCT AND ABRASION

ISSUE DATE: ☒ NA ☒ EMEA ☒ LATAM ☒ AP-Sep-23

IMPACTED REGIONS: ☐ DISCONTINUATION

REASON FOR CHANGE: ☒ OTHER

DESCRIPTION OF CHANGE: (Required)

Effective immediately, you may experience a slight color variation in our HSTT product offering. In addition, the customer drawing for the HSTTVA family is revised with a few minor dimensional changes for Nominal Recovered Wall Thickness.

Photos/Drawing (where applicable)

IMPACTED PART NUMBERS AND REPLACEMENT PART NUMBERS: (where applicable)

DATES: DISCONTINUATION AND NEW PRODUCT AVAILABILITY:

SCHEDULE FOR CHANGE	Year (YYYY)	Month (MM)	Day (DD)
New product sample availability date	2023	10	1
Old product discontinuation date*			

CUSTOMER SERVICE CONTACTS

ASIA PACIFIC	AUSTRALIA: 1-800 7263848 AUS-CSVM@panduit.com	CHINA: 400-820-1900 CHN-CustomerService@panduit.com	HONG KONG: 800-965768 CHN-CustomerService@panduit.com
	INDIA: 000 800 6501844 (Fixed) 000 800 6500369 (Mobile) SGP-Customer_Service@panduit.com	INDONESIA: 001 803 65 7571 SGP-Customer_Service@panduit.com	JAPAN: +81-3-6863-6000 JPN-CS@panduit.com
	KOREA: 02-2182-7300 KOR-CustomerService@panduit.com	MALAYSIA 1800 801435 SGP-Customer_Service@panduit.com	SINGAPORE: 1-800-7263848 SGP-Customer_Service@panduit.com
	TAIWAN: 0080 165 1487 SGP-Customer_Service@panduit.com	THAILAND: 001-800-65-6385 SGP-Customer_Service@panduit.com	
LATIN AMERICA	BRAZIL 08000562613 (Toll Free) BRA-custservice@panduit.com	MEXICO: +52-33-37776000 x80520 01 800 360 86 00 (Toll Free) MEX-customerservice@panduit.com	OTHER LA COUNTRIES: Phone USA 1-708-532-1800 TP-CS-INTERNATIONAL@panduit.com
NORTH AMERICA	USA & CANADA: 1-800-777-3300 cs@panduit.com	EMEA	EMEA: +44 208 6017219 EMEA-CustomerServices@panduit.com

IMPACTED PART NUMBER(s)	IMPACTED PART NUMBER(s)	IMPACTED PART NUMBER(s)	IMPACTED PART NUMBER(s)
HSTTVA12-48-Q	HSTT100-C6	HSTT200-48-5-6	HSTT50-48-Q10
HSTTVA19-48-Q	HSTT12-48-Q10	HSTT25-48-Q10	HSTT50-48-Q2
HSTTVA25-48-Q	HSTT12-48-Q2	HSTT25-48-Q2	HSTT50-48-Q4

HSTTV38-48-Q	HSTT12-48-Q4	HSTT25-48-Q4	HSTT50-48-Q5
HSTTV50-48-5	HSTT12-48-Q45	HSTT25-48-Q45	HSTT50-48-Q6
HSTTV75-48-5	HSTT12-48-Q5	HSTT25-48-Q5	HSTT50-C10
HSTTV100-48-5	HSTT12-48-Q6	HSTT25-48-Q6	HSTT50-C2
HSTTV150-48-5	HSTT12-C10	HSTT25-C10	HSTT50-C5
HSTT05-48-Q6	HSTT12-C2	HSTT25-C2	HSTT50-C6
HSTT06-48-Q2	HSTT12-C5	HSTT25-C5	HSTT50-T45
HSTT06-48-Q5	HSTT150-48-5	HSTT25-C6	HSTT75-48-5
HSTT06-48-Q6	HSTT150-48-5-10	HSTT38-48-Q10	HSTT75-48-5-10
HSTT06-C10	HSTT150-48-5-2	HSTT38-48-Q2	HSTT75-48-5-2
HSTT06-C4	HSTT150-48-5-4	HSTT38-48-Q4	HSTT75-48-5-4
HSTT06-C5	HSTT150-48-5-6	HSTT38-48-Q45	HSTT75-48-5-5
HSTT09-48-Q10	HSTT150-C2	HSTT38-48-Q5	HSTT75-48-5-6
HSTT09-48-Q2	HSTT150-C4	HSTT38-48-Q6	HSTT75-48-545
HSTT09-48-Q5	HSTT19-48-Q10	HSTT38-C10	HSTT75-C2
HSTT09-C5	HSTT19-48-Q2	HSTT38-C2	HSTT75-T45
HSTT100-48-5-10	HSTT19-48-Q4	HSTT38-C4	HSTT100-48-5-1
HSTT100-48-5-2	HSTT19-48-Q45	HSTT38-C5	HSTT100-48-5-3
HSTT100-48-5-4	HSTT19-48-Q5	HSTT38-C6	HSTT150-48-5-5
HSTT100-48-5-5	HSTT19-48-Q6	HSTT38-T45	HSTT19-48-Q1
HSTT100-48-5-6	HSTT19-C10	HSTT50-48-5	HSTT19-48-Q3
HSTT100-48-545	HSTT19-C2	HSTT50-48-5-10	HSTT25-48-Q1
HSTT100-C10	HSTT19-C5	HSTT50-48-5-2	HSTT25-48-Q3
HSTT100-C2	HSTT200-48-5-10	HSTT50-48-5-5	HSTT50-48-Q3
HSTT100-C45	HSTT200-48-5-2	HSTT50-48-5-6	HSTT75-48-5-1
HSTT100-C5	HSTT200-48-5-4	HSTT50-48-545	HSTT75-48-5-3