

# Adjustable Bayonet Thermocouple, Glassfibre Stainless Steel Overbraided Cable - IEC



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

# **Datasheet**



# Adjustable Bayonet Thermocouple with 200mm spring with adjustable fixing cap (11.5mm I.D. single slot)

# **Specifications**

General Description	Thermocouple with adjustable insertion depth			
Sensor Type	6.0mm diameter tip			
Thermocouple Type	KorJ			
Thermocouple Junction	Grounded tip for fast response			
Cable Length	2 or 3m			
Cable Type	Glassfibre insulated lead with stainless steel overbraid			
Core / Strands	7/0.2mm			
Termination Type	Standard Plug with Cable Clamps			
Max. Temperature	+350°C			
Min. Temperature	-60°C			
Standards Met	Colour code (cores & jacket) to IEC-584-3			
Bayonet cap	11.5mm I.D. single slot			
Tip	6.0mm diameter x 8mm long stainless steel			
Spring	6.0mm diameter x 200mm long overall			

# **Ordering Information**

Thermocouple Type	Cable Length	Termination	Manufacturers Code	Farnell Order Code
K	2m	Standard Plug	FS-GSK-6.0-2.0-C4-SP-I-Z Z=C/C	3584286
K	3m	Standard Plug	FS-GSK-6.0-3.0-C4-SP-I-Z Z=C/C	2785115
J	2m	Standard Plug	FS-GSJ-6.0-2.0-C4-SP-I-Z Z=C/C	2785114
J	3m	Standard Plug	FS-GSJ-6.0-3.0-C4-SP-I-Z Z=C/C	4073494

TC-2 Oct-23



#### Thermocouple & PRT Cable

Thermocouple cables are available in IEC or ANSI colour codes. Insulation types include PFA, PTFE, PVC &

Fibreglass. Available spool lengths include 10, 25, 50, 100 and 200m.

#### Best Sellers



**ANSI PTFE Insulated Twin Twisted** Farnell 2443696 Newark 73AC8304

**ANSI PFA Insulated** Twin Twisted Farnell 2443711 Newark 73AC8297

#### **Fabricated and Specialist Thermocouples**

Styles include; Magnet, Washer, Nozzle, Leaf, Bayonet & Bolt thermocouple. Various lengths and calibration types available.

# **Best Sellers**




Washer Thermocouple Farnell 8597952 Newark 38K1555



**Bayonet** Thermocouple Farnell 2785115 Newark 37AC0993

> Magnet Thermocouple Farnell 2081298 Newark 88T2877



Including exposed junctions with fitted or moulded miniature plug and insulated leads, ideal for test and development applications.

1, 2, 3, 5 & 10m lengths available in IEC or ANSI colours.

## **Best Sellers**





IEC Type K Exposed Junction Farnell 4100748 Newark 15J1022



#### Thermocouple Connectors

Range of miniature or standard thermocouple connectors. Available in thermocouple types K, J, T, E, N, RS, B, and copper. IEC, ANSI & JIS colour codes available.



#### **IEC Thermocouple PCB Socket** Farnell 2347056 **Newark 06X5514**



Plug Farnell 7086362 **Newark 67C1559** 





#### **RTD Detectors**

Wire-wound type provides greater accuracy and stability but are vulnerable to shock.

Flat film type are resistant to shock and have quicker thermal response times.

Various lengths and diameters available, in class A, B and 1/10th Din.

## **Best Sellers**



Farnell 8598550 Newark 38K0883

#### PT100 Wire **Wound Detector**

Farnell 2770776 Newark 25AC2608

PT100 Class A Thin Film Detector

Farnell 8598525 **Newark 38K0885** 



#### Mineral Insulated Thermocouples

Available in various calibration types with a variety of terminations.

These include; Thermocouple plugs, Terminal heads and Thermocouple cable.





IEC Thermocouple with Mini Plug

Farnell 4248338 **Newark 19J1166** 

**IEC Melt Bolt** Thermocouple Farnell 2816490 Newark 44AC8638



Resistance Thermometer Detectors (RTD) / Platinum Resistance Thermometers (PRT)

To suit a wide range of applications and styles, available in class A or B.

### Best Sellers



Pt100 Heavy Duty Sensor Probe Farnell 8598096 Newark 38K0974



Pt100 Outdoor/ Cold Store Temperature Sensor Farnell 2816462

Newark 44AC8648

# L60 Fine Wire

# Thermocouple Welder

The Thermocouple Welder is a compact, simple-to-use instrument designed for thermocouple and fine wire welding. Supplied with foot switch, spare electrodes, pliers & safety glasses, impact clip and pen plate.

# **Best Sellers**





L60+ Thermocouple & Fine Wire Welder and accessories Farnell 2897470 Newark 62AC8741

TC-2 Oct-23