

Bolt Thermocouple, Glassfibre Stainless Steel Over Braided Cable - ANSI



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

Datasheet



Bolt sensors are generally screwed into the surface which normally increases the speed of response and sensitivity of the measurement. Suitable for use up to +250°C.

Specifications

Thermocouple Type	К		
Thermocouple	Bolts have grounded junctions		
Junction			
Cable Length	2m		
Cable Type	Glassfibre stainless steel over braided cable		
Cable Termination	Bare Tails		
Max. Temperature	+250°C		
Standards Met	ANSI MC96.1		
Bolt thread/pitch	M8 x 1mm / M10 x 1mm / M12 x 1mm		
Colour	Positive: Red / Negative: Yellow		
Length	Bolt length: 13mm or 25mm		

Ordering Information

Туре	Cable Length	Bolt thread/pitch	Bolt length	Termination	Manufacturers Code	Farnell Order Code
К	2m	M8 x 1mm	13mm	Bare Tails	BT-GSK-M8F-13-2.0-C4-T-A	4155958
К	2m	M8 x 1mm	25mm	Bare Tails	BT-GSK-M8F-25-2.0-C4-T-A	4155959
К	2m	M10 x 1mm	13mm	Bare Tails	BT-GSK-M10F-13-2.0-C4-T-A	4155960
К	2m	M10 x 1mm	25mm	Bare Tails	BT-GSK-M10F-25-2.0-C4-T-A	4155961
К	2m	M12 x 1mm	13mm	Bare Tails	BT-GSK-M12F-13-2.0-C4-T-A	4155962
K	2m	M12 x 1mm	25mm	Bare Tails	BT-GSK-M12F-25-2.0-C4-T-A	4155963

