

Nozzle Thermocouple, Glassfibre insulated Cable with Stainless Steel Over-Braid Terminating in Bare tails, Miniature or Standard Plug- ANSI



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

Datasheet



Specifications

General Description	Thermocouple housed in a stainless steel threaded bolt			
Thermocouple Type	К			
Thermocouple Junction	Grounded hot junction for fast response, M6x1mm thread			
Cable Length	1, 2 or 5m			
Cable Type	Glassfibre insulated lead with stainless steel overbraid			
Core / Strands	7/0.2mm			
Termination Type	Bare tails, Miniature or Standard Plug (with cable clamps)			
Max. Temperature	+350°C			
Min. Temperature	-60°C			
Standards Met	ANSI MC96.1			
Thread	M6 x 1mm thread			

Ordering Information

Туре	Cable Length	Termination	Manufacturers Code	Farnell Order Code
К	1m	Bare Tails	FN-K-M-1.0-C4-T-A	4155787
К	2m	Bare Tails	FN-K-M-2.0-C4-T-A	4155788
K	5m	Bare Tails	FN-K-M-5.0-C4-T-A	4155789
К	1m	Miniature Plug	FN-K-M-1.0-C4-MP-A	4155790
К	2m	Miniature Plug	FN-K-M-2.0-C4-MP-A	4155791
K	5m	Miniature Plug	FN-K-M-5.0-C4-MP-A	4155792
К	1m	Standard Plug	FN-K-M-1.0-C4-SP-A-Z Z=C/C	4155793
К	2m	Standard Plug	FN-K-M-2.0-C4-SP-A-Z Z=C/C	4155794
К	5m	Standard Plug	FN-K-M-5.0-C4-SP-A-Z Z=C/C	4155795

