

Pipe Surface Thermocouple, Glassfibre stainless steel overbraid- JIS



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

Datasheet



Specifications

General Description	Stainless steel pipe clamp sensor with adjustable diameter		
Thermocouple Type	К		
Thermocouple Junction	Grounded tip for fast response		
Cable Length	2m		
Cable Type	Glassfibre stainless steel braided extension cable		
Core / Strands	7/0.2mm		
Termination Type	Bare tails		
Max. Temperature	+350°C		
To Fit Pipe Diameters	13-20mm, 22-30mm, 30-45mm and 40-55mm		
Standards Met	JIS		

Ordering Information

Туре	To Fit Pipe Diameters	Termination	Manufacturers Code	Farnell Order Code
K	13-20mm	Bare tails	FP-13/20-K-2M-J	4156036
K	22-30mm	Bare tails	FP-22/30-K-2M-J	4156037
K	30-45mm	Bare tails	FP-30/45-K-2M-J	4156038
K	40-55mm	Bare tails	FP-40/55-K-2M-J	4156039

TC-44 Nov-23



Thermocouple & PRT Cable

Thermocouple cables are available in IEC or ANSI colour codes. Insulation types include PFA, PTFE, PVC &

Fibreglass. Available spool lengths include 10, 25, 50, 100 and 200m.

Best Sellers



ANSI PTFE Insulated Twin Twisted Farnell 2443696 Newark 73AC8304

ANSI PFA Insulated Twin Twisted Farnell 2443711 Newark 73AC8297

Fabricated and Specialist Thermocouples

Styles include; Magnet, Washer, Nozzle, Leaf, Bayonet & Bolt thermocouple. Various lengths and calibration types available.


Best Sellers



Washer Thermocouple Farnell 8597952 Newark 38K1555



Magnet Thermocouple Farnell 2081298 Newark 88T2877



Including exposed junctions with fitted or moulded miniature plug and insulated leads, ideal for test and development applications.

1, 2, 3, 5 & 10m lengths available in IEC or ANSI colours.

Best Sellers



IEC Type T Exposed Junction Farnell 7076186 Newark 68C2613





Thermocouple Connectors

Range of miniature or standard thermocouple connectors. Available in thermocouple types K, J, T, E, N, RS, B, and copper. IEC, ANSI & JIS colour codes available.



IEC Thermocouple PCB Socket Farnell 2347056 **Newark 06X5514**



Farnell 7086362 Newark 67C1559





RTD Detectors

Wire-wound type provides greater accuracy and stability but are vulnerable to shock.

Flat film type are resistant to shock and have quicker thermal response times.

Various lengths and diameters available, in class A, B and 1/10th Din.

Best Sellers



PT1000 Thin Film Detector Farnell 8598550 Newark 38K0883

PT100 Wire **Wound Detector**

Farnell 2770776 Newark 25AC2608

PT100 Class A

Thin Film Detector Farnell 8598525 **Newark 38K0885**



Mineral Insulated Thermocouples

Available in various calibration types with a variety of terminations.

These include; Thermocouple plugs, Terminal heads and Thermocouple cable.





IEC Thermocouple with Mini Plug Farnell 4248338

Newark 19J1166

IEC Melt Bolt Thermocouple Farnell 2816490 Newark 44AC8638



Resistance Thermometer Detectors (RTD) / Platinum Resistance Thermometers (PRT)

To suit a wide range of applications and styles, available in class A or B.

Best Sellers



Pt100 Heavy Duty Sensor Probe Farnell 8598096 Newark 38K0974

Pt100 Sensor in Stainless Steel Tube with Teflon Lead Farnell 2420300 Newark 53X3459

Pt100 Outdoor/ Cold Store Temperature Sensor Farnell 2816462

Newark 44AC8648



L60 Fine Wire Thermocouple Welder

The Thermocouple Welder is a compact, simple-to-use instrument designed for thermocouple and fine wire welding. Supplied with foot switch, spare electrodes, pliers & safety glasses, impact clip and pen plate.

Best Sellers





L60+ Thermocouple & Fine Wire Welder and accessories Farnell 2897470 Newark 62AC8741

TC-44 Nov-23