

Washer Thermocouple, Glassfibre Insulated Cable with stainless steel overbraid- ANSI



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

Datasheet



Specifications

| General Description | Thermocouple housed in a washer eyelet | | |
|-------------------------|---|--|--|
| Thermocouple Type | К | | |
| Thermocouple | | | |
| Junction | Grounded tip for quick response | | |
| Cable Length | 2m | | |
| Cable Type | Glassfibre insulated, stainless steel overbraided | | |
| Core / Strands | 7/0.2mm | | |
| Termination Type | tion Type Either tails or standard plug termination with cable clamps | | |
| Max. Temperature | Temperature +350°C | | |
| Standards Met | ndards Met ANSI | | |
| | 3.5mm, 4.0mm, 5.0mm, 6.0mm, 8.0mm & 10.0mm clearance | | |
| Washer | hole available | | |

Ordering Information

| Туре | Washer Clearance Hole | Termination | Manufacturers Code | Farnell Order Code |
|------|-----------------------------|---------------|-------------------------------|-----------------------|
| K | 3.5mm | Bare Tails | FW-K-M3.5-2.0-C4-T-A | 4155824 |
| K | 4mm | Bare Tails | FW-K-M4-2.0-C4-T-A | 4155825 |
| K | 5mm | Bare Tails | FW-K-M5-2.0-C4-T-A | 4155826 |
| K | 6mm | Bare Tails | FW-K-M6-2.0-C4-T-A | 4155827 |
| K | 8mm | Bare Tails | FW-K-M8-2.0-C4-T-A | 4155829 |
| K | 10mm | Bare Tails | FW-K-M10-2.0-C4-T-A | 4155823 |
| K | 3.5mm | Standard Plug | FW-K-M3.5-2.0-C4-SP-A-Z Z=C/C | 4155832 |
| K | 4mm | Standard Plug | FW-K-M4-2.0-C4-SP-A-Z Z=C/C | 4155833 |
| K | 5mm | Standard Plug | FW-K-M5-2.0-C4-SP-A-Z Z=C/C | 4155834 |
| K | 6mm | Standard Plug | FW-K-M6-2.0-C4-SP-A-Z Z=C/C | 4155835 |
| K | 8mm | Standard Plug | FW-K-M8-2.0-C4-SP-A-Z Z=C/C | 4155836 |
| К | 10mm | Standard Plug | FW-K-M10-2.0-C4-SP-A-Z Z=C/C | 4155831 |

