

# multicomp PRO



## MP011887 3.7V USB LI-ION MINI GRINDER SET

### Specifications:

Speed controller : Push-on trigger switch  
Free running time of motor (rpm) : 6000~15000  
Power consumption of motor (W) : 0.5  
Housing material: ABS  
Charging socket: Micro USB  
Charging time: 2hrs

### Product Weight (w/o package) :

Weight(g)	Measurement		
	L(mm)	W(mm)	H(mm)
93	145	31	31

### Individual Packing

Packing: White Box + Label **Master Packing** :

	Pcs	N. W (Kg)	G. W (Kg)	Measurement			CUFT
				L(cm)	W(cm)	H(cm)	
Individual Packing	1	-	0.2	21	11.5	3.5	-
Inner Box	10	0.93	2.11	37	21	12.5	0.34
CTN	40	8	9.5	45	40	27.5	1.75



### INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.

When this product has reached the end of its life it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.



Made in China.  
PO Box 13362 Dublin 2  
LS22 2QQ