


PXPTPU78FBF04ACL050PUR Datasheet

Product Name // 4 Contacts 7/8" Flex Body Female 5m Cable

[View Product Page](#)



// Product Description:	
<ul style="list-style-type: none"> ⊕ 3 Contacts 7-8" Flex Body Female 5M Cable ⊕ IP67 rated when mated ⊕ Mechanical Cycles >100 	<ul style="list-style-type: none"> ⊕ Operating Temperature -25Å°C to +85Å°C ⊕ Rated Voltage 300 V ⊕ ROHS compliance

// General Information:	
Product Display Title:	7/8" Flex Body Female 5m Cable
Product Family:	Circular Automation Connectors
Product Series:	7/8" Series
Cable Length:	5m
Connection Method:	Solder
Contact Type:	Socket Contact
Current Max:	8A
Durability:	>100 Cycles
Function:	Flex Body Female Connector Single Ended Cable
Insulation Resistance:	>100MOhm
Ip Rating:	IP67
Max Cable Entry Size:	7.0mm
Max Operating Temperature:	+80°C
Min Operating Temperature:	-25°C
Number Of Contacts:	4 Contacts
Pin Layout Code:	A Code
Rohs Compliant:	Yes
Thread Size:	7/8-16UN
Voltage Max:	300V

// Product PDF Links

[78 Series Circular connectors...](#)