


PXPTPU78FBF05ACL050PUR Datasheet

Product Name // 5 Contacts 7/8" Flex Body Female 5m Cable

[View Product Page](#)



// Product Description:

- ⊕ 3 Contacts 7-8" Flex Body Female 5M Cable
- ⊕ Operating Temperature -25Å°C to +85Å°C
- ⊕ IP67 rated when mated
- ⊕ Rated Voltage 300 V
- ⊕ Mechanical Cycles >100
- ⊕ ROHS compliance

// General Information:

Product Display Title:	7/8" Flex Body Female 5m Cable
Product Family:	Circular Automation Connectors
Product Series:	7/8" Series
Cable Length:	5m
Connection Method:	Solder
Contact Type:	Socket Contact
Current Max:	9A
Durability:	>100 Cycles
Function:	Flex Body Female Connector Single Ended Cable
Insulation Resistance:	>100MOhm
Ip Rating:	IP67
Max Cable Entry Size:	8.5mm
Max Operating Temperature:	+80°C
Min Operating Temperature:	-25°C
Number Of Contacts:	5 Contacts
Pin Layout Code:	A Code
Rohs Compliant:	Yes
Thread Size:	7/8-16UN
Voltage Max:	300V

// Product PDF Links

[78 Series Circular connectors...](#)