


# PXPTPU78FIM03ACL020PUR Datasheet

**Product Name // 3 Contacts 7/8" Inline Body Male 2m Cable**

[View Product Page](#)



## // Product Description:

- ⊕ 3 Contacts 7-8" Inline Body Male 2m Cable
- ⊕ IP67 rated when mated
- ⊕ Mechanical Cycles >100
- ⊕ Operating Temperature -25Å°C to +85Å°C
- ⊕ Rated Voltage 300 V
- ⊕ ROHS compliance

## // General Information:

Product Display Title:	7/8" Inline Body Male 2m Cable
Product Family:	Circular Automation Connectors
Product Series:	7/8" Series
Cable Length:	2m
Connection Method:	Solder
Contact Type:	Plug Contact
Current Max:	12A
Durability:	>100 Cycles
Function:	Inline Body Male Connector Single Ended Cable
Insulation Resistance:	>100MOhm
Ip Rating:	IP67
Max Cable Entry Size:	6.5mm
Max Operating Temperature:	+80°C
Min Operating Temperature:	-25°C
Number Of Contacts:	3 Contacts
Pin Layout Code:	A Code
Rohs Compliant:	Yes
Thread Size:	7/8-16UN
Voltage Max:	300V

## // Product PDF Links

[78 Series Circular connectors...](#)



Have a question or project enquiry  
you'd like to talk to us about?



[Click Here To Contact Us](#)