Pushbutton Latching Switches

multicomp PRO



Specifications

Function Material Frame Actuator


Terminals

Rating	: 3A 125V AC, 1.5A 250V AC	
Contact Resistance	: 50mΩ Max.	
Insulation Resistance	: DC 500V 100MΩ Min.	
Dielectric Strength	: AC 1,000V 1 minute	
	AC 1,500V 1 minute Switch	
Function	: 2P SPST OFF-ON; LATCHING	
Material		
Frame	: Black, ABS	
Actuator	Plook APS	


: Black, ABS


: Silver Plated, Copper Alloy

Diagram




R13-23B-05-BR





15.5

R13-23B-05-BG



R13-23B-05-BW

Part Number Table

Description	Colour	Part Number
Pushbutton Switch, Latching, SPST, 3A 125V AC, 1.5A 250V AC	Red	R13-23B-05-BR
	Green	R13-23B-05-BG
	White	R13-23B-05-BW

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

multicomp PRO