


NSYSFNC125

Bottom and top frame, PanelSeT SFN, for electrical enclosure W1200 D500mm, roof included



Main

Range	PanelSeT
Accessory / separate part category	Enclosure accessory
Application	Multi-purpose
Product or component type	Framework kit
For enclosure nominal dimensions	- W: 1200 mm D: 500 mm
Mounting location	Top of vertical uprights Bottom of vertical uprights
Range compatibility	PanelSeT PanelSeT SFN
Device composition	1 bottom frame 1 roof 1 top frame
Quantity per set	Set of 1

Complementary

Material	Steel
Colour	Grey (RAL 7035)
Surface finish	Epoxy-polyester powder
Fixing mode	By screws - each corner of enclosure location
Height	110 mm
Width	1200 mm
Depth	500 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	121 cm
Package 1 Width	51 cm
Package 1 Length	15 cm
Package 1 Weight	20.7 kg
Unit Type of Package 2	P12
Number of Units in Package 2	8
Package 2 Height	121 cm
Package 2 Width	80 cm
Package 2 Length	145 cm
Package 2 Weight	178.9 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------
