



Main

Range	PanelSeT
Accessory / separate part category	Enclosure accessory
Product or component type	Door
Application	Multi-purpose
For enclosure nominal dimensions	- H: 2000 mm W: 400 mm
Mounting location	Front Side
Range compatibility	PanelSeT PanelSeT SFN
Device composition	4 locking bar catches 1 locking bar system 4 points 1 lock with handle and 5 mm double bar insert 1 door 4 hinges
Quantity per set	Set of 1

Complementary

Material	Sheet steel
Colour	Grey (RAL 7035)
Surface finish	Epoxy-polyester powder
Lock type	Lock 5 mm double bar
Number of locks	1
Door type	External plain
Door opening side	Reversible (120 °)
Height	1966 mm nominal:
Width	369 mm nominal:
Net weight	19.8 kg

Environment

IK degree of protection	IK10
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	200 cm
Package 1 Width	38 cm
Package 1 Length	6 cm
Package 1 Weight	17 kg
Unit Type of Package 2	P2M
Number of Units in Package 2	20
Package 2 Height	120 cm
Package 2 Width	200 cm
Package 2 Length	50 cm
Package 2 Weight	361 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------