



Main

Range	PanelSeT
Accessory / separate part category	Enclosure accessory
Product or component type	Door
Application	Multi-purpose
For enclosure nominal dimensions	- H: 2200 mm W: 1200 mm
Mounting location	Front
Range compatibility	PanelSeT PanelSeT SFN
Device composition	1 lock with handle and 5 mm double bar insert 1 locking bar system 4 points 2 door 1 locking bar system 2 points 2 reinforcement frame 8 hinges
Quantity per set	Set of 1

Complementary

Material	Sheet steel
Colour	Grey (RAL 7035)
Surface finish	Epoxy-polyester powder
Lock type	Lock 5 mm double bar
Number of locks	1
Door type	External plain
Door opening side	Reversible (120 °)
Maximum load	60 kg/m ²
Height	2166 mm nominal:
Width	1169 mm nominal:
Net weight	29.7 kg

Environment

IK degree of protection	IK10
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	220 cm
Package 1 Width	68 cm
Package 1 Length	10 cm
Package 1 Weight	52 kg
Unit Type of Package 2	P2M
Number of Units in Package 2	5
Package 2 Height	120 cm
Package 2 Width	223 cm
Package 2 Length	63 cm
Package 2 Weight	289 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------