

# Magnetic Transducer - 41.T70P015H-LF



■ MT Transducer 1.5V Pin Noryl Lead Free Material (RoHS)

■ Color - Black



## General Specification

Model Number	41.T70P015H-LF
Operating Voltage Range (V)	1.0 ~ 5.0
Rated Voltage (V)	1.5
Max. Rated Current <sup>+</sup> (mA)	30
Coil Resistance ( $\Omega$ )	16.0 +/- 4.5
Coil Impedance ( $\Omega$ )	40
Min. Sound Output at 10cm <sup>+</sup> (dBA)	85
Resonant Frequency (Hz)	2048
Operating Temperature ( $^{\circ}$ C)	-20 ~ +60
Terminal	Pin
Housing Material	Noryl
Weight (g)	2

+ Value applying rated voltage resonant frequency, 1/2 duty, square wave

\* Value applying resonant frequency, 1/2 duty, square wave, measuring current 60uA

## Dimension (mm)

