

9001KS43BH2

Selector switch, Harmony 9001K, metal, standard handle, black, 30mm, 3 positions, stay put, 2 C/O



Main

Bezel material	Chromium plated metal
Range of Product	K

Complementary

Line Rated Current	10 A
Accessory / separate part destination	Non illuminated push-button
Operator position information	3 positions
Operator profile	Standard knob
Operator profile	1 projecting push-button
Size	30 mm
Utilisation category	AC-15 DC-13

Environment

NEMA Degree of Protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	CSA LR 25490 class 3211 03[RETURN]CE[RETURN]UL listed file E42259 CCN NKCR

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	785901821342
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.90 in (4.826 cm)
Package 1 Width	2.20 in (5.588 cm)
Package 1 Length	3.70 in (9.398 cm)
Package 1 Weight	6.56 oz (185.973 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------