

INTRODUCTION

This small size breakout is programmable full-color RGB LED for hobbyists, industrial designers, prototypers, and experimenters. It is designed to allow the easy addition of dynamic indicators, displays, and lighting to existing or new projects. Controlled by PWM channels can be available in soft red, orange, yellow, green, blue and white...The high quality LED has wide viewing angle and optimized light coupling by inter reflector.

SPECIFICATION

- Full color RGB LED
- Operating Voltage:3.3-5V
- Wide viewing angle
- White package
- Operating Temperature:-40℃ to +85℃
- Size:13x13mm(0.51x0.51")

DOCUMENTS

- [3258 RGB LED dataset](#)
- [Wiki](#)

SHIPPING LIST

- RGB LED Breakout(3528) x1
- Straight pin header 4p x1