## 6442 Large Push Button



Technology Ltd

- Choice of button/escutcheon materials
- Choice of colours
- Choice of tube options
- Large air volume for longer tube lengths








## **General specifications**

Standards/ approvals	n/a
Connection method	Via back entry spout, 4mm dia. or 2mm dia.
Electrical rating	n/a
Contact configuration	See table
Pressure range	Compatible with 6871, 6872, 6773, 6753, 6891, 6893, 6861, 6862, 6863, 6864, 6869 – dependent on tube length

Operating temperature range	-10°C to +40°C
Body material	Thermoplastic
Weight	Plastic - 0.063Kg; metal - 0.2Kg
Additional information	Available as a vandal resistant version 6443

Recommended depression time is 30 seconds, for applications requiring a greater period please contact sales to discuss further.

## Reference dimensions in mm






## 6442 Large Push Button



Technology Ltd

**Ordering and options** 



Note: Button type "D" - metal and non-plated versions only
Button finish option 'P' - stainless steel can only be supplied as a flush button

For vandal resistant version, order 6443-0001, similar to 6442-DPPA-A000 (stainless)

